




IV CAVITY REFORM MOLD OF IV INFUSION REFORM WITH HANGER

腔PP大输液吊环 体瓶坯模具




**AVITY
MOLD**




匠心磨砺 中国质

100



72 CAVITY COLD HALF WITH EOAT PLATE AND COOLPIK PLATE


72腔冷模
配EOAT板
和CoolPik板



公司


发区兆丰路62号
nic development zone,
na
TEL:86-576-84360607
FAX:86-576-84330113
E-mail:admin@sicamold.com

**西卡模具
PET瓶坯模具工匠手艺**



old.com

www.sicamold.com



32 C
PRE
EOAT

32腔模
配EOA



SICAMOLD HISTORY

西卡模具发展史

2010

Sica established presentation of the first 48-cavity mold

西卡正式成立
第一套48腔模具发货

2014

Set up the first overseas office

成立第一个海外办事处

2016

Presentation of the first 72-cavity mold

第一套72腔模具发货

2022

144 cavity cold half for HyPET 500

144腔冷半模
用于HyPET 500

2018

Establish international standard quality control system

建立国际标准品控体系

2017

First 48-cavity cold half for HyPET 225

第一套48腔冷半模
For HYPET 225

BETTER TOOLS, BETTER WORKING


工欲善其事，必先利其器



STRICT QUALITY CONTROL SYSTEM 严格的质检体系


- Laboratory with high precision testing equipment.
- Taking international first-class standard as coordinate,
- Weeding out any inferior-quality workpiece through full inspection.

- 全系实验室高精密检验设备;
- 以国际一流标准为坐标;
- 用全检剔除每一件不达标工件。



ASSEMBLING WORKSHOP CONSTANT TEMPERATURE DUST-FREE

模具装配车间 — 恒温无尘



- Open the door of world-class preform mold, by Start from turning every screw properly.
- Strictly abide by the quality standards, never be "Mr. More or less".

- 从拧好每一颗螺丝开始，打开世界顶级瓶坯模具的大门。
- 严格遵守质量标准，坚决不做“差不多”先生。

